

# Hydrofoamer™ Part# 2BC802

## GENERAL SPECIFICATIONS AND USE

The Hydrofoamer connects to an air supply to provide a foaming application of many chemicals. Surface dwell time is extended and longer dwell periods mean better cleaning, through foam application. The Hydrofoamer substantially increases vertical and horizontal surface hang time. Liquid soap will streak vertical surfaces, foamed soap won't. Surface grime is released each time a foam bubble "explodes" which lifts the dirt to the surface. Controlled chemical concentration and air delivery means exact dilution ratios are achieved with the Hydrofoamer. Testing has shown that soap application via a foaming system can reduce soap usage by as much as 50%.

### Standard equipment:

- Adjustable soap mix from liquid to thick foam
- Air regulator
- Air pressure gauge
- Liquid pressure gauge
- Trigger gun and lance application unit
- 50' soap application hose

Choose your options (STD-designates the standard)

### Frame Configuration Options


- STD- Wall Mounted Foamer, No Pump  
OPT- Wall Mounted Foamer with Pump  
OPT- Portable Foamer with Pump

### Discharge Hose and Reel Options

- STD- 50' Dual Hose, No Reel  
OPT- Retract Reel with 50' Dual Hose  
OPT- Retract Reel with 75' Dual Hose  
OPT- Retract Reel with 100' Dual Hose

### Accessory Options

- OPT- Chemical Proportioning System, No Pump  
OPT- Chemical Proportioning with Pump (Will Supply Soap To 4 Wall Mount Foamers Without Pumps)  
OPT- Wand Holder, Wall Mount



865 West 2600 South, Salt Lake City, UT 84119  
Phone 800-247-8424 or 801-972-1181 Fax 801-972-3265

**HYDROBLASTERS - HYDROKLEEN - HYDROPAD**

[www.hydroblaster.com](http://www.hydroblaster.com)